

# Product data sheet

Specifications



## 10A 250V 1 Gang Bell Press Switch with Fluorescent Locator, White

E8231BPL1\_WE

### Main

Range	Pieno
Product or component type	Switch
Switch application	Bell
Load type	Resistive
Cover frame colour tint	White

### Complementary

Device mounting	Flush Surface
Wiring device mounting	Flush Surface
Switch function	Momentary
Rated current	10 A at 250 V AC 50 Hz
Local signalling	Fluorescent (white)
Number of gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	2 x 1.5 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s)
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	23 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	MS IEC 60669-1 BS EN 60669-1 GB 16915.1 IEC 60669-1 SS 227-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	89.64 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	717 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	7171.2 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)