

Product data sheet

Specifications



20A 250V 1 Gang Double Pole Switch with Neon, White

E8231D20N_WE

Main

Range	Pieno
Product or component type	Switch
Switch application	Switch
Load type	Resistive Fluorescent
Cover frame colour tint	White

Complementary

Device mounting	Flush Surface
Wiring device mounting	Surface Flush
Rated current	20 A at 250 V AC 50 Hz
Local signalling	Neon
Number of gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 1 x 6 mm ² for stranded cable(s)
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	32.2 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	GB 16915.1 SS 227-1 IEC 60669-1 MS IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	129.285 g
Package 1 Height	3.55 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)