

Product data sheet

Specifications



250V Illuminated "Privacy", "Pls Clean Up" & "Pls Wait" Symbols, White

E8231DMW_WE

Main

Range	Pieno
Product or component type	Indicator lamp
Cover frame colour tint	White

Complementary

Wiring device mounting	Flush Surface
Device mounting	Flush Surface
Local signalling	Please wait, neon (orange) Please clean up, neon (green) Privacy, neon (red)
[Ue] rated operational voltage	250 V AC 50 Hz
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	By screw
Clamping connection capacity	1 x 2.5 mm ² for solid cable(s) 1 x 1.5 mm ² for stranded cable(s)
Embedding depth	21 mm
Width	87 mm
Height	87 mm
Depth	30.1 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS EN 60669-1 SS 227-1 IEC 60669-1 MS IEC 60669-1 GB 16915.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	2.9 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	102.36 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	614 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6141.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)