

Product data sheet

Specifications



Pieno - 1 x 2.1A USB Charger - White

E8231USB_WE

Main

Range	Pieno
Product or component type	USB charger
Fixing mode	Screw

Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	White
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	1 module 46 x 36.7 x 21.7 mm
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	1 USB port 5 V DC, maximum load current: 2.1 A
Material	Silicone rubber: cover PC (polycarbonate): grid plate PC (polycarbonate): housing
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm ² for stranded cable(s) 2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s) 1.5 mm ² for stranded cable(s) 1.5 mm ² for flexible cable(s) 1.5 mm ² for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	HTC HW Power bank XiaoMi Apple Samsung Major smart phone and tablet
Standards	GB 4943.1

CNS 14336
CNS 13438
IEC 60950-1
MS IEC 60950-1

Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	27.3 mm
Net weight	0.0767 kg

Environment

Product certifications	CCC IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	83 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	664 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6.68 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Recommended replacement(s)