

# Product data sheet

Specifications



## Pieno - 2 x 2.1A USB Charger - White

E8232USB\_WE

### Main

Product or component type	USB charger
Fixing mode	Screw

### Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	White
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	2 modules 46 x 36.7 x 21.7 mm
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	PA (polyamide) 6: housing Silicone rubber: cover PC (polycarbonate): grid plate
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm <sup>2</sup> for stranded cable(s) 2.5 mm <sup>2</sup> for flexible cable(s) 2.5 mm <sup>2</sup> for rigid cable(s) 1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for flexible cable(s) 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	Power bank Samsung HW Apple Major smart phone and tablet XiaoMi HTC
Standards	CNS 14336 MS IEC 60950-1 GB 4943.1 IEC 60950-1

CNS 13438

Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	29.3 mm
Net weight	0.1107 kg

## Environment

Product certifications	IEC CCC
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	117.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	936 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	9.36 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

**Recommended replacement(s)**