

# Product data sheet

Specifications



## 16AX 250V 3 Gang 2 Way Switch with Fluorescent Locator, White

E8233L2F\_WE

### Main

|                           |                          |
|---------------------------|--------------------------|
| Range                     | Pieno                    |
| Product or component type | Switch                   |
| Switch application        | Switch                   |
| Load type                 | Fluorescent<br>Resistive |
| Cover frame colour tint   | White                    |

### Complementary

|                              |   |
|------------------------------|---|
| Device mounting              | Surface<br>Flush  |
| Wiring device mounting       | Flush<br>Surface  |
| Switch function              | 2-way   |
| Rated current                | 16 AX at 250 V AC 50 Hz   |
| Local signalling             | Fluorescent (white)   |
| Number of gangs              | 3 gangs   |
| Material                     | Polycarbonate: surround<br>Polycarbonate: grid plate  |
| Connections - terminals      | Pillar terminals  |
| Clamping connection capacity | 2 x 1.5 mm <sup>2</sup> for stranded cable(s)<br>2 x 2.5 mm <sup>2</sup> for solid cable(s) |
| Embedding depth              | 23 mm   |
| Width                        | 87 mm   |
| Height                       | 87 mm   |
| Depth                        | 23 mm   |

### Environment

|                                       |  |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...40 °C   |
| Relative humidity                     | 0...95 %   |
| Standards                             | GB 16915.1<br>IEC 60669-1<br>BS EN 60669-1<br>MS IEC 60669-1<br>SS 227-1 |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Weight             | 111.0 g    |
| Package 1 Height             | 3.6 cm     |
| Package 1 Width              | 8.7 cm     |
| Package 1 Length             | 8.7 cm     |
| Unit Type of Package 2       | PAL        |
| Number of Units in Package 2 | 1200       |
| Package 2 Weight             | 150437.6 g |
| Package 2 Height             | 86 cm      |
| Package 2 Width              | 80 cm      |
| Package 2 Length             | 120 cm     |
| Unit Type of Package 3       | BB1        |
| Number of Units in Package 3 | 6          |
| Package 3 Weight             | 667.0 g    |
| Package 3 Height             | 15 cm      |
| Package 3 Width              | 19 cm      |
| Package 3 Length             | 6 cm       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)