

Product data sheet

Specifications



10AX 250V 4 Gang 1 Way Switch with Fluorescent Locator, White

E8234L1F_WE

Main

Range	Pieno
Product or component type	Switch
Switch application	Switch
Load type	Fluorescent Resistive
Cover frame colour tint	White

Complementary

Device mounting	Surface Flush
Wiring device mounting	Surface Flush
Switch function	1-way
Rated current	10 AX at 250 V AC 50 Hz
Local signalling	Fluorescent (white)
Number of gangs	4 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s)
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	23 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	GB 16915.1 SS 227-1 MS IEC 60669-1 IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	115 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	711 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6897.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)