

Product data sheet

Specifications



10AX 250V 4 Gang 2 Way Switch with Fluorescent Locator, White

E8234L2F_WE

Main

| | |
|---------------------------|--------------------------|
| Range | Pieno |
| Product or component type | Switch |
| Switch application | Switch |
| Load type | Fluorescent Resistive |
| Cover frame colour tint | White |

Complementary

| | |
|------------------------------|---|
| Device mounting | Flush Surface |
| Wiring device mounting | Flush Surface |
| Switch function | 2-way |
| Rated current | 10 AX at 250 V AC 50 Hz |
| Local signalling | Fluorescent (white) |
| Number of gangs | 4 gangs |
| Material | Polycarbonate: surround Polycarbonate: grid plate |
| Connections - terminals | Pillar terminals |
| Clamping connection capacity | 2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) |
| Embedding depth | 23 mm |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 23 mm |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...40 °C |
| Relative humidity | 0...95 % |
| Standards | SS 227-1 IEC 60669-1 GB 16915.1 BS EN 60669-1 MS IEC 60669-1 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 124 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 6 |
| Package 2 Height | 15 cm |
| Package 2 Width | 19 cm |
| Package 2 Length | 6 cm |
| Package 2 Weight | 767 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 60 |
| Package 3 Height | 32.5 cm |
| Package 3 Width | 32.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 7418.4 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)