

Product data sheet

Specifications



115V/240V Universal Shaver Unit, Vertical, White

E82T727V_WE

Main

Product or component type	Universal shaver
Installation direction	Vertical
Input voltage	240 V AC 50 Hz
Output voltage	115 V AC 50 Hz
Transformer rated power in VA	20 VA
Load type	Non-polarised Polarised
Cover frame colour tint	White

Complementary

Material	Polycarbonate: surround Polycarbonate: grid plate
Width	147 mm
Height	87 mm
Depth	49.7 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 61558-2-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	577.5 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20

Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Package 2 Weight	11550 g
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	248000 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)