

# Product data sheet

Specifications



## 13A 1 Gang Switched Socket with Neon, Silver Bronze

E8415N\_SZ

### Main

|                           |                     |
|---------------------------|---------------------|
| Range                     | ZENcelo             |
| Product or component type | Power socket-outlet |
| Load type                 | Resistive           |
| Cover frame colour tint   | Silver bronze       |
| Cover plate colour tint   | Bronze              |

### Complementary

|                         |   |
|-------------------------|---|
| Device mounting         | Surface<br>Flush  |
| Local signalling        | Indicator light, neon (amber)   |
| Switch function         | 1-pole  |
| Rated current           | 13 A at 250 V AC 50 Hz  |
| Number of gangs         | 1 gang  |
| Material                | Brass contact<br>Phosphor contact<br>Polycarbonate base<br>Polycarbonate grid plate<br>Polycarbonate surround |
| Connections - terminals | Folded terminal   |
| Width                   | 87 mm   |
| Height                  | 87 mm   |
| Depth                   | 8 mm  |

### Environment

|                                       |  |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...40 °C   |
| Relative humidity                     | 0...95 %   |
| Environmental characteristic          | UV resistant indoor use  |
| Operating altitude                    | 2000 m   |
| Standards                             | BS 1363-2<br>MS 589<br>SS 145<br><br>SS 145<br>MS 589<br>BS 1363-2 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 3.0 cm    |
| Package 1 Width              | 8.72 cm   |
| Package 1 Length             | 8.72 cm   |
| Package 1 Weight             | 140.414 g |
| Unit Type of Package 2       | S04       |
| Number of Units in Package 2 | 80        |
| Package 2 Height             | 30 cm     |
| Package 2 Width              | 40 cm     |
| Package 2 Length             | 60 cm     |
| Package 2 Weight             | 11.708 kg |
| Unit Type of Package 3       | P12       |
| Number of Units in Package 3 | 1600      |
| Package 3 Height             | 125 cm    |
| Package 3 Width              | 105 cm    |
| Package 3 Length             | 80 cm     |
| Package 3 Weight             | 236.6 kg  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End of Life Information</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)