

Product data sheet

Specifications



13A 1 Gang Switched Socket with Neon, Silver Bronze

E8415N_SZ

Main

Range	ZENcelo
Product Or Component Type	Power socket-outlet
Load Type	Resistive
Cover Frame Colour Tint	Silver bronze
Cover Plate Colour Tint	Bronze

Complementary

Device Mounting	Surface Flush
Local Signalling	Indicator light, neon (amber)
Switch Function	1-pole
Rated Current	13 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - Terminals	Folded terminal
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	SS 145 MS 589 BS 1363-2

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	140.414 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	80
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.708 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1600
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	236.6 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	End of Life Information