

# Product data sheet

Specifications



## 13A 1 Gang Switched Socket with Indicator, White

E8415\_WE

### Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P
Load type	Resistive
Colour tint	White
Cover frame colour tint	White

### Complementary

Device mounting	Surface Flush
Local signalling	Mechanical indicator (amber)
Rated current	13 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal
Width	87 mm
Height	87 mm
Depth	8 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145  MS 589 SS 145 BS 1363-2

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	125.38 g
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9.17 kg
Unit Type of Package 3	P12
Number of Units in Package 3	1600
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	185 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)