

Product data sheet

Specifications



10A Full-Flat Bell Switch, White

E8431BP1_WE

Main

| | |
|---------------------------|--------------------------------|
| Range | ZENcelo |
| Product or component type | Switch |
| Device application | Bell switch |
| Load type | Resistive Incandescent lamp |
| Colour tint | White |
| Cover frame colour tint | White |

Complementary

| | |
|-------------------------|---|
| Device mounting | Surface Flush |
| Rated current | 10 A at 250 V AC 50/60 Hz |
| Number of gangs | 1 gang |
| Material | Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: surround |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 31 mm |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | 2000 m |
| Standards | IEC 60669-1 GB 16915.1 BS EN 60669-1 MS 60669-1 SS 227-1 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 98.927 g |
| Package 1 Height | 1.4 cm |
| Package 1 Width | 8.72 cm |
| Package 1 Length | 8.72 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 1.189 kg |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15.0 cm |
| Package 2 Length | 19.0 cm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Weight | 12392.7 g |
| Package 3 Height | 21.0 cm |
| Package 3 Width | 32.5 cm |
| Package 3 Length | 50.0 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)