

# Product data sheet

Specifications



## 1 Gang Bell Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Sym, White

E8431BPDM\_WE

### Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Resistive Inductive lamp
Colour tint	White
Cover frame colour tint	White

### Complementary

Device mounting	Flush Surface
Rated current	10 A at 250 V AC 50/60 Hz
Local signalling	Please clean up: indicator light, neon (green) Do not disturb: indicator light, neon (orange)
Number of gangs	1 gang
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60669-1 MS IEC 60669-1 BS EN 60669-1 GB 16915.1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	119.63 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	1.157 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	12070.4 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)