

Product data sheet

Specifications



1Gang Full-Flat Bell Switch w/ Illuminated "Do Not Disturb" Symbol, Silver Bronze

E8431BPD_SZ

Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Inductive lamp Resistive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Rated current	10 A at 250 V AC 50/60 Hz
Local signalling	Do not disturb: indicator light, neon (orange)
Number of gangs	1 gang
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	MS IEC 60669-1 IEC 60669-1 BS EN 60669-1 GB 16915.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	97.3 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	978.4 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	10284 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)