

Product data sheet

Specifications



1 Gang CATV Socket, Silver Bronze

E8431CATV_SZ

Main

Range	ZENcelo
Product or component type	TV/FM/SAT socket
TV connector	F connectors
SAT connector	CATV
Colour tint	Silver bronze

Complementary

Device mounting	Surface Flush
Socket number	1 45° ground lug
Number of gangs	1 gang
Material	Polycarbonate: cover
Bandwidth	5...862 Hz
Maximum insertion loss	1 dB
Connections - terminals	F connectors: clamps terminal Saddle terminal: clamps terminal Inner: pillar terminal without pressure plate
Width	87 mm
Height	87 mm
Depth	37.4 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	BS 3041

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm

Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	127.76 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	966.56 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	10165.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)