

Product data sheet

Specifications



20A 1 Gang Full-Flat Double Pole Switch with Neon, White

E8431D20_WE

Main

Range	ZENcelo
Product or component type	Switch
Load type	Inductive
Colour tint	White
Cover frame colour tint	White

Complementary

Device mounting	Surface Flush
Rated current	20 A at 250 V AC 50/60 Hz
Number of gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: dolly Polycarbonate: surround
Connections - terminals	Brass rod terminals
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	31.5 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	GB 16915.1 MS IEC 60669-1 IEC 60669-1 SS 227-1 BS EN 60669-1

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	126.5 g
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	12.17 kg
Unit Type of Package 3	P12
Number of Units in Package 3	1600
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	245.976 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)