

# Product data sheet

Specifications



## 45A 1G FULL-FLAT DP ROCKER SWITCH W/NEON

E8431D45\_SZ

### Main

Range	ZENcelo
Product or component type	Switch
Load type	Resistive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

### Complementary

Device mounting	Flush Surface
Rated current	45 A at 250 V AC 50/60 Hz
Local signalling	Indicator light, neon (amber)
Number of gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - terminals	Brass rod terminals
Embedding depth	22 mm
Width	87 mm
Height	87 mm
Depth	30.2 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	IEC 60669-1 BS EN 60669-1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	161.72 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.493 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	15437.6 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)