

Product data sheet

Specifications



45A 1G FULL-FLAT DP ROCKER SWITCH W/NEON

E8431D45_WE

Main

Range	ZENcelo
Product or component type	Switch
Load type	Resistive
Colour tint	White
Cover frame colour tint	White

Complementary

Device mounting	Flush Surface
Rated current	45 A at 250 V AC 50/60 Hz
Local signalling	Indicator light, neon (amber)
Number of gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - terminals	Brass rod terminals
Embedding depth	22 mm
Width	87 mm
Height	87 mm
Depth	30.2 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	161.72 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.493 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	15437.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)