

Product data sheet

Specifications



1 Gang Full-Flat Switch with Illuminated "Do Not Disturb" Symbol, Silver Bronze

E8431DS_SZ

Main

| | |
|---------------------------|--|
| Range | ZENcelo |
| Product or component type | Switch |
| Load type | Incandescent lamp Fluorescent lamp Inductive |
| Colour tint | Silver bronze |
| Cover frame colour tint | Silver bronze |

Complementary

| | |
|-------------------------|---|
| Device mounting | Surface Flush |
| Rated current | 16 AX at 250 V AC 50/60 Hz |
| Local signalling | Do not disturb: indicator light, neon (amber) Please clean up: indicator light, neon (green) |
| Number of gangs | 1 gang |
| Material | Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround |
| Connections - terminals | Brass rod terminals |
| Width | 43.9 mm |
| Height | 50.7 mm |
| Depth | 1.8 mm |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | 2000 m |
| Standards | BS EN 60669-1 IEC 60669-1 GB 16915.1 SS 227-1 MS IEC 60669-1 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 8.72 cm |
| Package 1 Length | 8.72 cm |
| Package 1 Weight | 89.8 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 15 cm |
| Package 2 Width | 19 cm |
| Package 2 Length | 8 cm |
| Package 2 Weight | 918 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 32.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 9684 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)