

# Product data sheet

Specifications



## Illuminated "Do Not Disturb" Symbol, Silver Bronze

E8431D\_SZ

! Discontinued on: 17 December 2020

! Discontinued

### Main

Range	ZENcelo
Product or component type	Message indicator
Local signalling	Do not disturb: indicator light, neon (orange)
Colour tint	Silver bronze

### Complementary

Device mounting	Flush Surface
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
[Ue] rated operational voltage	250 V AC 50/60 Hz
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Illuminated indicators: folded terminal
Embedding depth	19.57 mm
Width	87 mm
Height	87 mm
Depth	27.72 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
Standards	IEC 60669-1 EN 60669-1 MS IEC 60669-1 GB 16915.1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	89.05 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)