

Product data sheet

Specifications



ZENcelo - 1 x 2.1A USB Charger - White

E8431USB_WE

Main

Product or component type	USB charger
Device presentation	Mechanism
Colour tint	White
Number of terminals	2 screw terminals

Complementary

Device mounting	Flush
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	1 module 46 x 36.7 x 21.7 mm
Fixing mode	Screw
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	1 USB port 5 V DC, maximum load current: 2.1 A
Material	Silicone rubber: cover PC (polycarbonate): grid plate PC (polycarbonate): housing
Shape of screw head	Cross
Clamping connection capacity	2.5 mm ² for stranded cable(s) 2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s) 1.5 mm ² for stranded cable(s) 1.5 mm ² for flexible cable(s) 1.5 mm ² for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	Power bank Apple Major smart phone and tablet XiaoMi HW HTC Samsung
Height	87 mm
Width	87 mm
Depth	37.1 mm
Embedding depth	27.3 mm
Net weight	0.0773 kg

Environment

Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
Product certifications	IEC CCC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	83 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	666 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6.68 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)