

Product data sheet

Specifications



ZENcelo - 16AX 250V - 1 gang 1 way switch (SZ)

E8431_1_R_SZ_C1

⚠ Discontinued on: May 24, 2017

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Switch
Switch Function	1-way
Number Of Gangs	1 gang

Complementary

Device Mounting	Surface Flush
Type Of Packing	Blister
Rated Current	20 A at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Material	Grid plate: polycarbonate + GF 20 % Base: polycarbonate Cover: polycarbonate Surround: polycarbonate
Load Type	Fluorescent lamp Resistive Inductive Incandescent lamp
Cover Frame Colour Tint	Silver bronze
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	Dust resistant
Operating Altitude	2000 m
Standards	MS IEC 60669-1 EN 60669-1 GB 16915.1 IEC 60669-1 SS 227-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications