

Product data sheet

Specifications



20A 2 Gang Full-Flat Double Pole Switch with Neon, Silver Bronze

E8432D20_SZ

Main

Range	ZENcelo
Product or component type	Switch
Device application	Control
Load type	Inductive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

Complementary

Number of rocker	2
Device mounting	Surface Flush
Rated current	20 A at 250 V AC 50/60 Hz
Number of gangs	2 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: dolly Polycarbonate: surround
Connections - terminals	Brass rod terminals
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	31.5 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	SS 227-1 GB 16915.1 EN 60669-1 MS IEC 60669-1 IEC 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	169.42 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)