

Product data sheet

Specifications



2 Gang Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Symbols, Silver Bronze

E8432DMS_SZ

Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Resistive Inductive lamp
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

Complementary

Device mounting	Surface Flush
Rated current	10 A at 250 V AC 50/60 Hz
Local signalling	Please clean up: indicator light, neon (green) Do not disturb: indicator light, neon (orange)
Number of gangs	2 gangs
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60669-1 BS EN 60669-1 MS IEC 60669-1 GB 16915.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	113.8 g
Unit Type of Package 2	PAL
Number of Units in Package 2	4800
Package 2 Height	120.0 cm
Package 2 Width	120.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	701240.0 g
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Height	15.0 cm
Package 3 Width	19.0 cm
Package 3 Length	8.0 cm
Package 3 Weight	1.11 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)