

Product data sheet

Specifications



Illuminated "Do Not Disturb" & "Please Clean Up" Symbols, Silver Bronze

E8432DM_SZ

Main

Range	ZENcelo
Product or component type	Message indicator
Local signalling	Please clean up: indicator light, neon (green) Do not disturb: indicator light, neon (orange)
Colour tint	Silver bronze

Complementary

Device mounting	Surface Flush
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
[Ue] rated operational voltage	250 V AC 50/60 Hz
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Illuminated indicators: folded terminal
Embedding depth	19.57 mm
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
Standards	MS IEC 60669-1 GB 16915.1 EN 60669-1 IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	96.48 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	971.84 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	10218.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)