

Product data sheet

Specifications



ILLUMINATED DND & PCU SYMBOLS

E8432DM_WE

! Discontinued on: 30 September 2022

! Discontinued

Main

| | |
|---------------------------|--------------------------------------------------------------------------------------------------|
| Range | ZENcelo |
| Product or component type | Message indicator |
| Local signalling | Please clean up: indicator light, neon (green) Do not disturb: indicator light, neon (orange) |
| Colour tint | White |

Complementary

| | |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting | Flush Surface |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| [Ue] rated operational voltage | 250 V AC 50/60 Hz |
| Material | Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround |
| Connections - terminals | Illuminated indicators: folded terminal |
| Embedding depth | 19.57 mm |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 27.72 mm |

Environment

| | |
|---------------------------------------|-----------------------------------------------------------|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | <= 2000 m |
| Standards | IEC 60669-1 GB 16915.1 MS IEC 60669-1 EN 60669-1 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 8.72 cm |
| Package 1 Length | 8.72 cm |
| Package 1 Weight | 111.12 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 1.088 kg |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 32.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 11389.6 g |

Offer Sustainability

| | |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)