

Product data sheet

Specifications



2G TEL SOCKET ON SHUTTERED WALLPLATE

E8432RJS4_SZ

Main

Range	ZENcelo
Product or component type	Telephone socket
Socket additional information	Shuttered
Number of gangs	2 gangs
Colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Rated current	1.5 A
Contact resistance	1 μ Ohm
Insulation resistance	\geq 200 MOhm
Minimum return loss	23 dB
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Environmental characteristic	No UV resistant
Relative humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	109.81 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8

Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.078 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	11284.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)