

Product data sheet

Specifications



2 Gang Telephone Socket on Shuttered Wallplate, White

E8432RJS4_WE

Main

Range	ZENcelo
Product or component type	Telephone socket
Socket additional information	Shuttered
Number of gangs	2 gangs
Material	PC: housing Polycarbonate: plastic part
Colour tint	White

Complementary

Device mounting	Surface Flush
Communication network category	Voice: 3
Rated current	1.5 A
Contacts material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Contact resistance	1 μ Ohm
Insulation resistance	\geq 200 MOhm
Minimum return loss	23 dB
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 (4 twisted pair cables)
Environmental characteristic	No UV resistant
Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.72 cm
Package 1 Length	8.72 cm
Package 1 Weight	109.81 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.078 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	11284.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)