

Product data sheet

Specifications



ZENcelo - 2 x 2.1A USB Charger - Silver Bronze

E8432USB_SZ

Main

Product or component type	USB charger
Device presentation	Mechanism
Colour tint	Silver bronze
Number of terminals	2 screw terminals

Complementary

Device mounting	Flush
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	2 modules 46 x 36.7 x 21.7 mm
Fixing mode	Screw
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	PA (polyamide) 6: housing Silicone rubber: cover PC (polycarbonate): grid plate
Shape of screw head	Cross
Clamping connection capacity	2.5 mm ² for stranded cable(s) 2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s) 1.5 mm ² for stranded cable(s) 1.5 mm ² for flexible cable(s) 1.5 mm ² for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	Major smart phone and tablet XiaoMi Apple HTC Samsung HW Power bank
Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	29.3 mm
Net weight	0.1113 kg

Environment

Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
Product certifications	CCC IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	122.0 g
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Weight	976.0 g
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Weight	9760.0 g
Package 3 Height	21.0 cm
Package 3 Width	31.0 cm
Package 3 Length	50.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)