

# Product data sheet

Specifications



## ZENcelo - 16AX 250V - 2 gang 2 way switch without indicator (WE)

E8432\_2\_R\_WE\_C1

⚠ Discontinued on: May 24, 2017

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Switch
Switch Function	2-way
Number Of Gangs	2 gangs

### Complementary

Device Mounting	Surface Flush
Type Of Packing	Blister
Rated Current	20 A at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Material	Grid plate: polycarbonate + GF 20 % Base: polycarbonate Cover: polycarbonate Surround: polycarbonate
Load Type	Inductive Fluorescent lamp Incandescent lamp Resistive
Cover Frame Colour Tint	White
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	Dust resistant
Operating Altitude	2000 m
Standards	IEC 60669-1 MS IEC 60669-1 SS 227-1 GB 16915.1 EN 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications