

Product data sheet

Specifications



TV/FM/Satellite TV Socket without Looping, Silver Bronze

E8433SMATV_SZ

! Discontinued on: 06 March 2019

! End-of-service on: 17 September 2019

! Discontinued

Main

Range	ZENcelo
Product or component type	TV/FM/SAT socket
TV socket type	TV/FM/SAT
TV connector	Male IEC
Radio connector	Female IEC
SAT connector	Female F type
Additional information	Without looping With passage of 500 mA current for distributed power supply
Colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Average impedance	75 Ohm
Material	Polycarbonate: grid plate Polycarbonate: surround
Minimum return loss	5 dB 40...2400 kHz IN 5 dB 40...862 kHz TV 5 dB 950...2400 kHz SAT 8 dB 87.5...125 kHz FM-SAT
Isolation	> 20 at 88...108 kHz (TV-FM) > 30 at 40...860 kHz (FM-SAT) > 6 at 40...2400 kHz (TV-SAT)
Width	87 mm
Height	87 mm
Depth	36.2 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	87.5 g

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)