

Product data sheet

Specifications



16A 250V 1 Gang 3 Pin Universal Socket with Shutter, Sliver White

E84426UEST_SW

⚠ Discontinued on: Feb 17, 2017

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E American
Load Type	Resistive
Cover Frame Colour Tint	Silver white
Cover Plate Colour Tint	White

Complementary

Device Mounting	Surface Flush
Rated Current	16 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Brass metal parts Nylon + GF shutter Steel metal parts PC base PC cover
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	29 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	IEC 60884-1
Standards	IEC 60884-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	79 g

Contractual warranty

Warranty	18 months
----------	-----------