

Product data sheet

Specifications



13A Twin Gang Switched Socket with Indicator, Silver Bronze

E84T25_SZ

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Surface Flush
Local signalling	Mechanical indicator (amber)
Rated current	13 A at 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Brass contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround Phosphor bronze contact
Connections - terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145 SS 145 MS 589 BS 1363-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	205.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	10.0 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	1225.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)