

Product data sheet

Specifications



Universal Shaver Unit, Horizontal, Silver Bronze

E84T727H_SZ

Main

Range	ZENcelo
Product or component type	Shaver socket
Installation direction	Horizontal
Input voltage	240 V AC 50 Hz
Output voltage	115 V AC 50 Hz 240 V AC 50 Hz
Material	Polycarbonate: base Polycarbonate: grid plate Polycarbonate: surround
Colour tint	Silver bronze

Complementary

Device mounting	Surface Flush
Cable cross section	1...2.5 mm ²
Rated operational power in VA	20 VA
Connections - terminals	Pillar terminal without pressure plate
Electrical insulation class	Class B
Width	147 mm
Height	87 mm
Depth	49.3 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
IP degree of protection	IP21
Standards	IEC 61558-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	605.66 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Package 2 Weight	12113.2 g
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	242264 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)