

# Product data sheet

Specifications



## Universal Shaver Unit, Vertical, White

E84T727V\_WE

### Main

Range	ZENcelo
Product or component type	Shaver socket
Installation direction	Vertical
Input voltage	240 V AC 50 Hz
Output voltage	115 V AC 50 Hz 240 V AC 50 Hz
Material	Polycarbonate: base Polycarbonate: grid plate Polycarbonate: surround
Colour tint	White

### Complementary

Device mounting	Flush Surface
Cable cross section	1...2.5 mm <sup>2</sup>
Rated operational power in VA	20 VA
Connections - terminals	Pillar terminal without pressure plate
Electrical insulation class	Class B
Width	147 mm
Height	87 mm
Depth	49.3 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
IP degree of protection	IP21
Standards	IEC 61558-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	658.1 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Package 2 Weight	11713.2 g
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	263240 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)