

Product data sheet

Specifications



Asfora - 1pole 2way switch, screwless terminals, IP44, aluminium

EPH0400461

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

| | |
|---------------------------|--|
| Range | Asfora |
| Product Or Component Type | Switch |
| Device Presentation | Complete product |
| Number Of Rocker | 1.0 |
| Switch Function | 1-pole 2-way |
| Load Type | Load for energy saving lamps with ballast: 100 W |
| Colour Tint | Aluminium |
| Type Of Packing | Flow-pack |

Complementary

| | |
|-------------------------|---------------------------------------|
| Device Mounting | Flush |
| Power Range | 2300 W |
| Rated Current | 10 AX at 250 V AC |
| Number Of Cables | 2 cable(s) 2.5 mm ² |
| Cable Stiffness | Flexible Rigid Solid stranded |
| Wire Stripping Length | 13.0 mm |
| Material | ABS (acrylonitrile butadiene-styrene) |
| Surface Finish | Painted |
| Conductor Material | Copper |
| Fixing Mode | Screws or claws51...70 mm |
| Connections - Terminals | Screwless terminals |
| Width | 83 mm |
| Height | 83 mm |
| Depth | 43.0 mm |
| Projecting Depth | 15 mm |
| Net Weight | 0.0858 kg |

Environment

| | |
|-----------|-------------|
| Standards | IEC 60669-1 |
|-----------|-------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|------------------|
| Product Certifications | TSE VDE NF |
| Quality Labels | CE UKR |
| Ip Degree Of Protection | IP44 |
| Ambient Air Temperature For Operation | -5...40 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.0 cm |
| Package 1 Width | 8.0 cm |
| Package 1 Length | 8.0 cm |
| Package 1 Weight | 88.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 18.5 cm |
| Package 2 Length | 27.5 cm |
| Package 2 Weight | 954.0 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 120 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 40.0 cm |
| Package 3 Length | 60.0 cm |
| Package 3 Weight | 12.065 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |