

# Product data sheet

Specifications



## 13A Twin 3 Pin Switched Socket Outlet, White

ET3025\_WW

### Main

Range	Neo C-Metro
Product or component type	Power socket-outlet
Switch function	1-pole
Outlet poles configuration	3P with shutters
Outlet standard	BS 1363 SS 145 MS 589
Colour tint	White

### Complementary

Wiring device mounting	Surface Flush
Rated current	13 A at 250 V AC 50/60 Hz
Material	Brass: contact Copper with silver onlay: bridge Nylon: shutter Polycarbonate: grid plate Polycarbonate: surround Steel with brass plating: screws Steel with brass plating: terminals
Load type	Resistive
Connections - terminals	Pillar terminals
Width	147 mm
Height	87 mm
Depth	18 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	BS 1363 SS 145 MS 589

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	300.0 g
Package 1 Height	2.2 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)