

# Product data sheet

Specifications



## Shaver Unit 115/240V, Grey Silver

ET3727V\_GS

### Main

Range of product	Neo C-Metro
Product or component type	Shaver socket
Input voltage	250 V AC 50 Hz
Colour tint	Grey silver

### Complementary

Wiring device mounting	Surface Flush
Output voltage	115 V AC 50 Hz type A 115 V AC 50 Hz type C 240 V AC 50 Hz
Transformer rated power in VA	20 VA
Material	Polycarbonate: plastic part
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Electrical insulation class	Class B
Width	87 mm
Height	147 mm
Depth	57 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 61558-2-5 IEC 61558-1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	826.69 g
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	16533.8 g
Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Weight	330676.0 g
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)