

# Product data sheet

Specifications



## Shaver Unit 115/240V, White

ET3727V\_WW

### Main

Range Of Product	Neo C-Metro
Product Or Component Type	Shaver socket
Input Voltage	250 V AC 50 Hz
Colour Tint	White

### Complementary

Wiring Device Mounting	Flush Surface
Output Voltage	115 V AC 50 Hz type A 115 V AC 50 Hz type C 240 V AC 50 Hz
Transformer Rated Power In Va	20 VA
Material	Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Electrical Insulation Class	Class B
Width	87 mm
Height	147 mm
Depth	57 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	IEC 61558-2-5 IEC 61558-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.7 cm
Package 1 Weight	826.39 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Package 2 Weight	16527.8 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	400
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	330556 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	<a href="#">End of Life Information</a>