

Product data sheet

Specifications



Shaver Unit 115/240V, White

ET3727V_WW

Main

Range of product	Neo C-Metro
Product or component type	Shaver socket
Input voltage	250 V AC 50 Hz
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Output voltage	115 V AC 50 Hz type A 115 V AC 50 Hz type C 240 V AC 50 Hz
Transformer rated power in VA	20 VA
Material	Polycarbonate: plastic part
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Electrical insulation class	Class B
Width	87 mm
Height	147 mm
Depth	57 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 61558-2-5 IEC 61558-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	826.39 g
Package 1 Height	4.9 cm
Package 1 Width	14.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	16527.8 g
Package 2 Height	16.3 cm
Package 2 Width	33 cm
Package 2 Length	50.4 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	400
Package 3 Weight	330556.0 g
Package 3 Height	86 cm
Package 3 Width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)