

Product data sheet

Specifications



Miniature circuit breaker (MCB), Easy9, 2P, 6A, C curve, 6000A (IEC/EN 60898-1)

EZ9F56206

Main

Range	Easy9
Device application	Distribution
Product or component type	Miniature circuit-breaker
Device short name	Easy9 MCB
Poles	2P
Number of protected poles	2
[In] rated current	6 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	10000 A Icn at 220 V AC 50/60 Hz conforming to IEC 60898-1 6000 A Icn at 400 V AC 50/60 Hz conforming to IEC 60898-1
Suitability for isolation	Yes conforming to IEC 60898-1

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	220 V AC 50/60 Hz 400 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6 kA 100 % x Icn at 230 V AC 50/60 Hz conforming to IEC 60898-1
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60898-1
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60898-1
Contact position indicator	Yes
Control type	Toggle
Local signalling	Without
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	81 mm

Width	36 mm
Depth	66.5 mm
Colour	Grey (RAL 7035)
Mechanical durability	10000 cycles
Electrical durability	4000 cycles
Connections - terminals	Tunnel type terminal (top or bottom) 1...25 mm ² rigid Tunnel type terminal (top or bottom) 1...16 mm ² flexible
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Without

Environment

Standards	IEC 60898-1
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2
Tropicalisation	2
Relative humidity	95 % at -5...60 °C
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	3.6 cm
Package 1 Length	8.5 cm
Package 1 Weight	208 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	8 cm
Package 2 Width	8.8 cm
Package 2 Length	22.6 cm
Package 2 Weight	1.314 kg
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14.976 kg

Recommended replacement(s)