

Product data sheet

Specifications



busbar Easypact - 250 A - 4 ways

EZB250W04

⚠ Discontinued on: Mar 31, 2021

⚠ Discontinued

Main

Range Of Product	EasyPact
Range	EasyPact
Device Short Name	busbar
Product Or Component Type	Busbar
Device Application	Connection
Range Compatibility	EasyPact EasyPact EZB circuit breaker
[In] Rated Current	250 A
Number Of Ways	4 ways

Complementary

[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz
[Ue] Rated Operational Voltage	550 V AC 50/60 Hz
Number Of Devices	12 (1P) 4 (3P) 6 (2P)
Busbar Extension	Without
[Icw] Rated Short-Time Withstand Current	30 kA for 1 s
Height	268.5 mm
Width	416 mm
Depth	82.5 mm

Environment

Standards	IEC 60439
-----------	-----------

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	