

# Product data sheet

Specifications



## Detector base sounder, BSO-PP-N33, without isolator

FFS06711722

### Main

Range Of Product	Esmi addressable components for SLC range
Product Or Component Type	Mounting base

### Complementary

Product Destination	Audible alarm
Colour Tint	Body: pure white Base: pure white
[Ue] Rated Operational Voltage	15...32 V DC
Current Consumption	120 µA standby alarm
Signalling Type	32 tones alarm
Acoustic Level	92...98 dBA at 1 m
Type Of Setting	Volume: low settings Volume: medium settings Volume: high settings
Cable Cross Section	1.5...2.5 mm²
Diameter	121 mm
Height	64 mm (low profile) 119 mm (deep base) 119 mm (waterproof base)
Net Weight	202 g

### Environment

Standards	EN 54-3
Product Certifications	LPCB CPD
Ip Degree Of Protection	IP24 with low profile base IP44 with deep base IP65 with waterproof base
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature For Operation	-25...70 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	12.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	228.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information