

Product data sheet

Specifications



MGE Galaxy 7000 Static Bypass Switch

G7TSBS

⚠ Discontinued on: Oct 18, 2023

⚠ Discontinued

Overview

Presentation	Centralized static switch cubicles (IP20 or IP32) for parallel configurations providing the highest energy availability
Lead Time	Special Order - Call for Quoted Lead Times

Main

Provided Equipment	User manual
--------------------	-------------

Physical

Mounting Mode	Not rack-mountable
---------------	--------------------

Conformance

Product Certifications	CE LCIE
Standards	EN 60950 EN/IEC 62040-2 EN/IEC 62040-3 ISO 14001 ISO 9001

Environmental

Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	20...80 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	20...80 %
Storage Altitude	0.00...9144.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.01 cm
Package 1 Width	0.01 cm
Package 1 Length	0.01 cm
Package 1 Weight	2195.387 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------