

Product data sheet

Specifications



Ultimate - Switched Socket 2 USB charger - 2 gang - 13A - metallic - white

GGBGU34202USBWPN

Main

Range	Ultimate
Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket with USB charger
Device Presentation	Complete product
Device Application	USB charger
Colour Tint	Front plate: pearl nickel Interior: white
Surface Finish	Metallic
Connections - Terminals	Screw terminals
Switch Function	1-pole
Rated Current	13 A at 220...240 V AC 50/60 Hz

Complementary

Device Mounting	Flush Surface
Outlet Standard	BS 1363
Integrated Connection Type	2 socket-outlet 220...250 V AC 13 A 50/60 Hz 2 USB port 5 V DC 2.1 A
Actuator	Rocker
Number Of Gangs	2 gangs
Pilot Light	Silver without LED
Fixing Mode	2 screw: M3.5 26 mm diameter: 3.5 mm 2 screw: M3.5 32 mm diameter: 3.5 mm
Clamping Connection Capacity	2 x 6 mm² for solid cable(s) 3 x 4 mm² for solid cable(s) 5 x 2.5 mm² for solid cable(s) 3 x 4 mm² for stranded cable(s) 5 x 2.5 mm² for stranded cable(s)
Socket Additional Information	Earthed
Earth Circuit	Standard earth
Material	Stainless steel
Product Compatibility	Mobile/tablet Apple Mobile/tablet Samsung Mobile/tablet LG Mobile/tablet Blackberry Mobile/tablet HTC Mobile/tablet Sony Mobile/tablet Huawei Technologies

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2019/1782/EC - ecodesign
Quality Labels	CE
Quantity Per Set	Set of 1
Type Of Packing	Box
Type Of Installation	Indoor
Depth	35 mm
Width	147.5 mm
Height	87.5 mm
Net Weight	0.29 kg

Environment

Ip Degree Of Protection	IP20
Standards	BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	9.7 cm
Package 1 Length	15.5 cm
Package 1 Weight	341 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	17.5 cm
Package 2 Width	43 cm
Package 2 Length	50.5 cm
Package 2 Weight	17.72 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1000
Package 3 Height	104 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	374.4 kg

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div></div> <div>Rohs Exemption Information</div> <div>Yes</div>	
<hr/>	
Reach Regulation	REACH Declaration
<hr/>	
Eu Rohs Directive	Compliant
	EU RoHS Declaration
<hr/>	
China Rohs Regulation	China RoHS declaration
<hr/>	