

# Product data sheet

Specifications



Plate switch, Ultimate Flat plate, 2-way retractive, screw terminals, IP20, brass

GU1212RBPB

## Main

Range Of Product	Ultimate
Range	Ultimate
Aesthetic Name	Flat plate
Product Or Component Type	Plate switch
Control Type	Rocker
Switch Function	2-way retractive
Rated Current	16 AX at 230 V AC

## Complementary

Connections - Terminals	Screw terminals
Material	Steel
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Device Mounting	Wall mounted
Height	88 mm
Width	88 mm
Depth	24 mm

## Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.200 cm
Package 1 Width	4.000 cm
Package 1 Length	10.100 cm
Package 1 Weight	126.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	23.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	43.500 cm
Package 2 Length	52.500 cm
Package 2 Weight	20.356 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	115.000 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	325.696 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)