

Product data sheet

Specifications



Plate switch, Ultimate Flat plate, 2-way, screw terminals, IP20, pearl nickel

GU1212WPN

Main

Range Of Product	Ultimate
Range	Ultimate
Device Application	Control
Aesthetic Name	Flat plate
Product Or Component Type	Plate switch
Control Type	Rocker
Switch Function	2-way
Rated Current	16 AX at 230 V AC

Complementary

Connections - Terminals	Screw terminals
Material	Stainless steel
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Device Mounting	Wall mounted
Height	88 mm
Width	88 mm
Depth	24 mm

Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.600 cm
Package 1 Weight	148.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	21.000 cm
Package 2 Width	42.500 cm
Package 2 Length	50.000 cm
Package 2 Weight	15.460 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	267.360 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration