

# Product data sheet

Specifications



Switch, Ultimate Flat plate, 2-pole,  
screw terminals, IP20, white metal

GU2213WPW

## Main

Range Of Product	Ultimate
Range	Ultimate
Aesthetic Name	Flat plate
Product Or Component Type	Switch
Switch Function	2-pole
Rated Current	20 AX at 230 V AC

## Complementary

Connections - Terminals	Screw terminals
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Height	88 mm
Width	88 mm

## Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.100 cm
Package 1 Width	10.100 cm
Package 1 Length	10.300 cm
Package 1 Weight	159.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	23.000 cm
Package 2 Width	43.500 cm
Package 2 Length	52.500 cm
Package 2 Weight	23.556 kg
Unit Type Of Package 3	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	1600
Package 3 Height	115.000 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	376.896 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Circularity Profile	No need of specific recycling operations