

# Product data sheet

Specifications



Switched socket, Ultimate  
Screwless flat plate, 2P, screw  
terminal, IP20, chrome

GU3410DBPC

## Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Chrome polished

## Complementary

Device Presentation	Complete product
Outlet Poles Configuration	2P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Steel
Quantity Per Set	Set of 1
Height	88 mm
Width	88 mm
Depth	30 mm
Socket Number	2

## Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	9.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	217.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.000 cm
Package 2 Width	42.000 cm
Package 2 Length	50.000 cm
Package 2 Weight	22.300 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	376.800 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>